



Self-levelling hot plate dispenser trolleys

CPC2-28, CPC2-34, CPC4-28

**Installation, operation and maintenance
manual**

Warranty

Edesa Hostelera S.A. assumes liability for manufacturing defects only. This warranty excludes, therefore, any liability for the incorrect handling or operation of the equipment by the customer or user. This warranty will remain in effect for a period of six months and will cover components with manufacturing defects only. Labour and transport costs are the exclusive responsibility of the customer in all cases. Edesa does not accept any responsibility for defects attributable to transport unless claims are made within 24 hours of receipt of the goods.

Specifications

- Trolleys specially designed to heat, transport, store and distribute plates or similar items.
- Trolleys manufactured from 18/10 stainless steel internally and externally.
- Manufactured with double wall and interior insulation.
- Adjustment system for different plate sizes. The required diameter can be regulated with 3 adjustable rods that act as guides for stacking plates.
- Elasticity can be adjusted by activating or deactivating the springs (heat resistant), guaranteeing that plates are served at the same level at all times.
- Approximate capacity: 45 plates per column.
- Thermostat temperature control.
- The temperature range is between +30°C C and +90°C.
- The trolley is equipped with 4 125-mm-diameter, noiseless, swivel-mounted casters, two of which are fitted with brakes.
- Non-marking rubber bumpers on the 4 corners

CPC2-28

Heating elements: 2 of 480W

Consumption: 4.4A

CPC2-34

Heating elements: 2 of 480W

Consumption: 4.4A


CPC4-28

Heating elements: 4 of 480W

Consumption: 8.8A

Operation

1. The height of the plates is adjusted by means of springs. According to the weight and diameter of the plates it is necessary to adjust the amount of springs for every requirement. Access is gained to the springs through the top of the trolley.(1) While making these adjustments, make sure that the plates are distributed symmetrically around the perimeter to prevent these from tilting to one side when placed on the base.
2. The plates are heated by means of elements placed in the bottom of the dispenser. Should it be necessary to gain access to the heating elements do this by removing the screws situated in the bottom of the dispenser (2).
3. In order to gain access to the electrical installation of the appliance, remove the handle and control panel (3).



1. Connect the TROLLEY to the electrical network (230V). The connection to earth is mandatory.
2. Connect the trolley using the **main switch**
3. Select the working temperature by turning the thermostat knob over the reference point.
4. The pilot light next to the thermostat indicates the operation of the resistances.

Caution

Attention: Due to this trolley is destined to heat, the whole interior is a high temperature zone. **Avoid direct contact and extreme precautions**

For any manipulation of the heating system, or operations that require it, the trolley **must be disconnected from the electrical network**.

At the moment of removing the plates from the inside of the trolley, pay attention to the interior temperature.


ELECTRICAL DIAGRAM – PLATE DISPENSER TROLLEY

Mod. CPC2

1. Switch
2. Thermostat
3. 220V/480W heating element
4. Thermostat pilot light
5. 3-pole terminal block
6. Safety thermostat

ELECTRICAL DIAGRAM – CPC4

1. Switch
 2. Thermostat
 3. 220V/480W heating element
 4. Thermostat pilot light
 5. 4-pole terminal block
 6. Safety thermostat
- Contactor





DECLARACIÓN DE CONFORMIDAD CE

Edenox.

Carretera Córdoba – Málaga Km. 80.800
14900 Lucena
(Córdoba)
Spain
edenox@edenox.com

**declara bajo su responsabilidad que los carros calientes de su
fabricación:**

Modelos / Models: **CPC2-28 , CPC2-34 , CPC4-28**

**cumplen con la directiva del Consejo de Europa:
*comply with the directive of the Council of***

EN-60335-1 Seguridad / Security

89/392/CEE Directiva Seguridad General Máquinas / *General Safety of
Machines Directive*

Barcelona
Fecha / Date: 14/03/2017

Lluís Bertomeu
Product Manager